

HTRA2 Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant Human HtrA2 Protein (Ala134-Glu458)
Form	Liquid
Concentration	Lot-Specific
Storage conditions	Maintain refrigerated at 2-8°C for up to 1 month. For long term storage store at -20°C
RRID	AB_2787984


Applications	Tested Dilution	Publications
Western Blot (WB)	1:500-1:1,000	-
Immunohistochemistry (Paraffin) (IHC (P))	1:2,000-1:10,000	-
ELISA (ELISA)	1:25000-1:50000	-
Immunoprecipitation (IP)	0.2-1 µL/mg of lysate	-

Product Specific Information


This product is preservative free. It is recommended to add sodium azide to avoid contamination (final concentration 0.05% -0.1%).

This antibody has specificity for Human HtrA2.


Product Images For HTRA2 Polyclonal Antibody



HTRA2 Antibody (PA5-80699) in IHC (P)
Immunohistochemical staining of human HTRA2 in human kidney with HTRA2 Polyclonal Antibody (Product # PA5-80699, 1:5,000 dilution, formalin-fixed paraffin embedded sections).



HTRA2 Antibody (PA5-80699) in WB
Western Blot using HTRA2 Polyclonal Antibody (Product # PA5-80699) at 1:500 dilution. Lane A: HL60 Whole Cell Lysate, Lane B: Jurkat Whole Cell Lysate, Lane C: Hela Whole Cell Lysate. Lysates/proteins at 30 g per lane. Secondary Goat Anti- Rabbit IgG H&L (DyLight™ 800) at 1:10,000 dilution. Developed using the Odyssey technique. Performed under reducing conditions. Predicted band size: 49 kDa. Observed band size: 37 kDa.



HTRA2 Antibody (PA5-80699) in IP
HTRA2 Immunoprecipitation using: Lane A: 0.5 mg Jurkat Whole Cell Lysate 0.5 μL with HTRA2 Polyclonal Antibody (Product # PA5-80699) and 15 μL of 50 % Protein G agarose. Primary antibody: HTRA2 Polyclonal Antibody, at 1:500 dilution. Secondary antibody: Clean-Bloto IP Detection Reagent (HRP) at 1:1,000 dilution. Developed using the DAB staining technique. Performed under reducing conditions. Predicted band size: 37 kDa. Observed band size: 37 kDa.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.