

SOD1 Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Recombinant protein corresponding to Human SOD1
Form	Liquid
Concentration	0.1 mg/mL
Purification	Anitgen affinity chromatography
Storage buffer	PBS, pH 7.2, with 40% glycerol
Contains	0.02% sodium azide
Storage conditions	Store at 4°C short term. For long term storage, store at -20°C, avoiding freeze/thaw cycles.
RRID	AB_2789100

Applications	Tested Dilution	Publications
Western Blot (WB)	0.04-0.4 µg/mL	-
Immunohistochemistry (IHC)	1:1,000-1:2,500	-
Immunocytochemistry (ICC/IF)	0.25-2 µg/mL	-


Product Specific Information

Immunogen sequence: PVQGIINFEQ KESNGPVKVW GSIKGLTEGL HGFHVHEFGD NTAGCTSAGP HFNPLSRKHG
GPKDEERHVG DLGNVTADKD GVADVSIEDS VISLSGDHCI IGRTLVVHEK ADDLGKGGNE ESTKTGNAGS RLACG

Product Images For SOD1 Polyclonal Antibody


SOD1 Antibody (PA5-81939)

Antibody specificity was demonstrated by siRNA mediated knockdown of target protein. Hep-G2 cells were transfected with, control siRNA, SOD1 siRNA probe #1, and SOD1 siRNA probe #2 and a decrease in signal intensity was observed in Western Blot application using anti-SOD1 Polyclonal Antibody (Product # PA5-81939) used at a dilution of 0.4 µg/mL. Anti-SOD1 was used as a loading control. {KD}




SOD1 Antibody (PA5-81939) in WB

Western blot was performed using Anti-SOD1 Polyclonal Antibody, (Product # PA5-81939) and a ~16 kDa band corresponding to SOD1 was observed across the cell lines tested. Whole cell extracts (30 µg lysate) of HAEC (Lane1), A549 (Lane 2), HCT 116 (Lane 3), MCF-7 (Lane 4) and U-2OS (Lane 5) were electrophoresed using Novex® NuPAGE® 4-12 % Bis-Tris gel (Product # NP0321BOX). Resolved proteins were then transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with the primary antibody (0.4 µg/mL) and detected by chemiluminescence with Goat anti-Rabbit IgG (Heavy Chain) Superclonal™ Recombinant Secondary Antibody, HRP (Product # A27036, 1:4000 dilution) using the iBright FL 1000 (Product # A32752). Chemiluminescent detection was performed using Novex® ECL Chemiluminescent Substrate Reagent Kit (Product # WP20005).



SOD1 Antibody (PA5-81939) in WB

Western blot analysis (Fig a) of SOD1 was performed on cell extracts (30 µg of lysate) of HeLa wild type (Lane 1) and SOD1 knockout (Lane 2). The blot was probed with the Anti-SOD1 Polyclonal Antibody (Product # PA5-81939, 0.4 µg/mL) and detected by chemiluminescence with Goat anti-Rabbit IgG (Heavy Chain), Superclonal™ Recombinant Secondary Antibody, HRP (Product # A27036, 1:4000 dilution) using the iBright FL 1000 (Product # A32752)) using the iBright FL 1000 (Product # A32752). Loss of signal upon CRISPR mediated knockout (KO) confirms that antibody is specific to SOD1.



[View more figures on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.