


CD4 Monoclonal Antibody (S3.5), Qdot 800

Product Details	
Size	25 µL
Species Reactivity	Human
Host/Isotype	Mouse / IgG2a
Class	Monoclonal
Type	Antibody
Clone	S3.5
Conjugate	Qdot® 800
Immunogen	Human CD4
Form	Liquid
Purification	purified
Storage buffer	0.05M borate, pH 8.3, with 1M betaine
Contains	0.05% sodium azide
Storage conditions	4° C
RRID	AB_2556509

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	Assay-dependent	1 Publication

Product Images For CD4 Monoclonal Antibody (S3.5), Qdot 800



CD4 Antibody (Q22153) in Flow

Histogram of gated human lymphocytes labeled with CD4 Mouse Anti-Human mAb (clone S3.5), Qdot® 800 Conjugate. Sample was acquired and analyzed using 405 nm excitation and a 780/60 band pass emission filter using a BD LSR II flow cytometer (BD Biosciences, San Jose, CA).

Flow Cytometry (1)

Journal of immunological methods

Quantum dots thermal stability improves simultaneous phenotype-specific telomere length measurement by FISH-flow cytometry.

"Q22153 was used in flow cytometry to study the improvement of simultaneous phenotype-specific telomere length measurement by FISH-flow cytometry by quantum dots thermal stability"

Authors: Kapoor V, Hakim FT, Rehman N, Gress RE, Telford WG

Species
Not Applicable

Dilution
Not Cited

Year
2009

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.