

Human IL-23 Recombinant Protein, PeproTech®

Product Details

Size	2 x 500 µg
Species	Human
Published Species	Human, Mouse
Expression system	Insect cells
Amino acid sequence	p19 subunit: RAVPGGSSPA WTQCQQLSQK LCTLAWSAHP LVGHMDLREE GDEETTNDVP HIQCGDGCDF QGLRDNSQFC LQRIHQGLIF YEKLLGSDIF TGEPSLLPDS PVGQLHASLL GLSQLLQPEG HHWETQQIPS LSPSQPWQRL LLRFKILRSL QAFVAVAARV FAHGAATLSP p40 subunit: IWELKKDVYV VELDWPDPAP GEMVLTCDT PEEDGITWTL DQSSEVLGSG KTLTIQVKEF GDAGQYTCHK GGEVLSHSL LLHKKEDGIW STDILKDQKE PKNKTFLRCE AKNYSGRFTC WWLTTISTDL TFSVKSSRGS SDPQGVTCGA ATLSAERVGR DNKEYEYSVE CQEDSACPAE EESLPIEVMV DAVHKLKYEN YTSSFFIRDI IKPDPPKNLQ LKPLKNSRQV EVSWEYPDTW STPHSYFSLT FCVQVQGKSK REKKDRVFTD KTSATVICRK NASISVRAQD RYYSSSWSEW ASVPCS
Molecular weight	53.5 kDa
Class	Recombinant
Type	Protein
Purity	95% by SDS-PAGE gel and HPLC analyses.
Endotoxin concentration	<1 EU/µg
Activity	Measured by its ability to induce IL-17 secretion by mouse splenocytes.
Conjugate	Unconjugated
Form	Lyophilized
Purification	HPLC, SDS-PAGE
Contains	no preservative
Storage conditions	-20°C

Applications	Tested Dilution	Publications
Functional Assay (FN)	Assay-dependent	-
In vitro Assay (IV)	-	79 Publications
Miscellaneous PubMed (Misc)	-	3 Publications

Product Specific Information

200-23-1MG will be provided as 2 x 500 µg (200-23-500UG).

Recombinant Human IL-23 is a 53.5 kDa, heterodimeric protein consisting of the two subunits, p19 (170 amino acids) and p40 (306 amino acids).

This product is shipped at ambient temperature. For storage, handling and reconstitution information, please see the lot-specific Certificate of Analysis

In vitro Assay (79)

<p>International journal of biological sciences</p> <p>Targeting Aquaporin-3 Attenuates Skin Inflammation in Rosacea.</p> <p>"200-23 was used in Cell Culture to reveal that AQP3-mediated activation of NF-B in keratinocytes and activation of STAT3 in CD4+ T cells acted synergistically and contributed to the inflammation in rosacea."</p> <p>Authors: Chen M,Peng Q,Tan Z,Xu S,Wang Y,Wu A,Xiao W,Wang Q,Xie H,Li J,Shi W,Deng Z</p>	<p>Year 2023</p> <p>Species Human</p>
<p>Cellular and molecular gastroenterology and hepatology</p> <p>Tofacitinib-Induced Modulation of Intestinal Adaptive and Innate Immunity and Factors Driving Cellular and Systemic Pharmacokinetics.</p> <p>"200-23 was used in In vitro experiments to describe an unappreciated mechanism-namely induction of equilibrative nucleoside transporters-enhancing baseline cellular uptake that can be inhibited pharmaceutically."</p> <p>Authors: Texler B,Zollner A,Reinstadler V,Reider SJ,Macheiner S,Jelusic B,Pfister A,Watschinger C,Przywiecki N,Tilg H, Oberacher H,Moschen AR</p>	<p>Year 2022</p> <p>Species Human</p>

[View more IV references on thermofisher.com](#)

Miscellaneous PubMed (3)

<p>Viruses</p> <p>Host Cell Redox Alterations Promote Latent HIV-1 Reactivation through Atypical Transcription Factor Cooperativity.</p> <p>"200-23 was used in Cell Culture to suggest that manipulation of redox-sensitive pathways could be exploited to alter the course of HIV-1 latency, thus rendering host cells responsive to help achieve a sterilizing cure."</p> <p>Authors: Cruz-Lorenzo E,Ramirez NP,Lee J,Pandhe S,Wang L,Hernandez-Doria J,Spivak AM,Planelles V,Petersen T, Jain MK,Martinez ED,D'Orso I</p>	<p>Year 2022</p> <p>Species Human</p>
<p>Journal of immunology (Baltimore, Md. : 1950)</p> <p>Pathogenic Role of an IL-23/T17/Neutrophil Axis in Coxsackievirus B3-Induced Pancreatitis.</p> <p>Authors: Yan K,Yang J,Qian Q,Xu D,Liu H,Wei L,Li M,Xu W</p>	<p>Year 2019</p> <p>Species Mouse</p>

[View more Misc references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.