

Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor™ 555

Product Details	
Size	1 mg
Species Reactivity	Mouse
Host/Isotype	Goat / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	Alexa Fluor™ 555
Excitation/Emission Max	553/568 nm
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Liquid
Concentration	2 mg/mL
Purification	purified
Storage buffer	PBS, pH 7.5
Contains	5mM sodium azide
Storage conditions	4° C, store in dark
RRID	AB_2535844

Applications	Tested Dilution	Publications
Western Blot (WB)	-	0 Publication
Immunohistochemistry (IHC)	1-10 µg/mL	0 Publication
Immunohistochemistry (Paraffin) (IHC (P))	-	0 Publication
Immunohistochemistry (Frozen) (IHC (F))	-	0 Publication
Immunohistochemistry - Free Floating (IHC (Free))	-	0 Publication
Immunocytochemistry (ICC/IF)	2 µg/mL	0 Publication
Flow Cytometry (Flow)	1-10 µg/mL	0 Publication
Miscellaneous PubMed (Misc)	-	0 Publication

Product Specific Information

To minimize cross-reactivity, these goat anti-mouse IgG (H+L) whole secondary antibodies have been affinity purified and cross-adsorbed against human IgG and human serum prior to conjugation. Cross-adsorption or pre-adsorption is a purification step to increase specificity of the antibody resulting in higher sensitivity and less background staining. The secondary antibody solution is passed through a column matrix containing immobilized serum proteins from potentially cross-reactive species. Only the nonspecific-binding secondary antibodies are captured in the column, and the highly specific secondaries flow through. The benefits of this extra step are apparent in multiplexing/multicolor-staining experiments (e.g., flow cytometry) where there is potential cross-reactivity with other primary antibodies or in tissue/cell fluorescent staining experiments where there may be the presence of endogenous immunoglobulins.

Alexa Fluor dyes are among the most trusted fluorescent dyes available today. Invitrogen™ Alexa Fluor 555 dye is a bright, orange-fluorescent dye with excitation ideally suited to the 555 nm laser line. For stable signal generation in imaging and flow

cytometry, Alexa Fluor 555 dye is pH-insensitive over a wide molar range. Probes with high fluorescence quantum yield and high photostability allow detection of low-abundance biological structures with great sensitivity. Alexa Fluor 555 dye molecules can be attached to proteins at high molar ratios without significant self-quenching, enabling brighter conjugates and more sensitive detection. The degree of labeling for each conjugate is typically 2-8 fluorophore molecules per IgG molecule; the exact degree of labeling is indicated on the certificate of analysis for each product lot.


Using conjugate solutions: Centrifuge the protein conjugate solution briefly in a microcentrifuge before use; add only the supernatant to the experiment. This step will help eliminate any protein aggregates that may have formed during storage, thereby reducing nonspecific background staining. Because staining protocols vary with application, the appropriate dilution of antibody should be determined empirically. For the fluorophore-labeled antibodies a final concentration of 1-10 µg/mL should be satisfactory for most immunohistochemistry and flow cytometry applications.

Product will be shipped at Room Temperature.




Product Images For Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor™ 555

Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody (A-21422) in ICC/IF

Immunofluorescence analysis of Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor® 555 conjugate was performed using HeLa cells stained with alpha Tubulin (236-10501) Mouse Monoclonal Antibody (Product # A11126). The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 10 minutes, blocked with 1% BSA for 1 hour and labeled with 2 µg/mL primary antibody for 3 hours at room temperature. Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor® 555 (Product # A-21422) was used at a concentration of 2 µg/mL in phosphate buffered saline containing 0.2% BSA for 45 minutes at room temperature, for detection of alpha Tubulin in the cytoplasm (Panel a: red). Nuclei (Panel b: blue) were stained with DAPI in SlowFade® Gold Antifade Mountant (Product # S36938). F-actin was stained with Alexa Fluor® 488 Phalloidin (Product # A12379), 1:300 (Panel c: green). Panel d represents the composite image. No nonspecific staining was observed with the secondary antibody alone (panel f), or with an isotype control (panel e). The images were captured at 60X magnification.



Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody (A-21422) in ICC/IF
HeLa cell transfected with pShooter pCMV/myc/mito/GFP, then fixed and permeabilized. Green-fluorescent protein (GFP) localized in the mitochondria was labeled with anti-GFP mouse IgG_{2a} (Product # A-11120) and detected with orange-fluorescent Alexa Fluor® 555 goat anti-mouse IgG (Product # A-21422), which colocalized with the dim GFP fluorescence. F-actin was labeled with green-fluorescent Alexa Fluor® 488 phalloidin (Product # A12379), and the nucleus was stained with blue-fluorescent DAPI (Product # D1306, D3571, D21490). The sample was mounted using ProLong® Gold antifade reagent (Product # P36930). Some GFP fluorescence is retained in the mitochondria after fixation (top), but immunolabeling and detection greatly improve visualization (bottom).



Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody (A-21422) in ICC/IF
Immunofluorescent analysis of CD44 (red) in human bone marrow derived mesenchymal stem cells. The cells were fixed with 2% paraformaldehyde, and blocked with 2% normal donkey serum diluted in PBS for 30 minutes at room temperature. Cells were stained with a CD44 monoclonal antibody (Product # MA5-12394) at a dilution of 10 µg/mL in blocking buffer for 1 hour at room temperature, and then incubated with a Goat anti-mouse IgG (H+L) Secondary Antibody, Alexa Fluor® 555 conjugate (Product # A-21422) at a dilution of 1:800 for 1 hour at room temperature (red). Nuclei (blue) were stained with Hoechst 33342 dye (Product # 62249). Note: Data courtesy of Innovators Program.

[View more figures on thermofisher.com](https://www.thermofisher.com)

1209 References

Regulation of proteostasis by sleep through autophagy in *Drosophila* models of Alzheimer's disease. *Life Sci Alliance* (2024)

Functional Neuroligin-2-MDGA1 interactions differentially regulate synaptic GABAARs and cytosolic gephyrin aggregation. *Commun Biol* (2024)

Microglial morphological/inflammatory phenotypes and endocannabinoid signaling in a preclinical model of periodontitis and depression. *J Neuroinflammation* (2024)

Calaxin is a key factor for calcium-dependent waveform control in zebrafish sperm. *Life Sci Alliance* (2024)

Altered expression of the Plexin-B2 system in tuberous sclerosis complex and focal cortical dysplasia IIb lesions. *Histol Histopathol* (2024)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.