

Donkey anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor™ 647

Product Details	
Size	1 mg
Species Reactivity	Mouse
Host/Isotype	Donkey / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	Alexa Fluor™ 647
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Liquid
Concentration	2 mg/mL
Purification	purified
Storage buffer	PBS, pH 7.5
Contains	5mM sodium azide
Storage conditions	4° C, store in dark
RRID	AB_162542

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	1-10 µg/mL	-
Immunocytochemistry (ICC/IF)	2 µg/mL	-
Flow Cytometry (Flow)	1-10 µg/mL	-

Product Specific Information

To minimize cross-reactivity, these donkey anti-mouse IgG whole antibodies have been affinity-purified and show minimum cross-reactivity to bovine, chicken, goat, guinea pig, hamster, horse, human, rabbit, rat, and sheep serum proteins. Cross-adsorption or pre-adsorption is a purification step to increase specificity of the antibody resulting in higher sensitivity and less background staining. The secondary antibody solution is passed through a column matrix containing immobilized serum proteins from potentially cross-reactive species. Only the nonspecific-binding secondary antibodies are captured in the column, and the highly specific secondaries flow through. The benefits of this extra step are apparent in multiplexing/multicolor-staining experiments (e.g., flow cytometry) where there is potential cross-reactivity with other primary antibodies or in tissue/cell fluorescent staining experiments where there may be the presence of endogenous immunoglobulins.

Alexa Fluor dyes are among the most trusted fluorescent dyes available today. Invitrogen™ Alexa Fluor 647 dye is a near-infrared-fluorescent dye with excitation ideally suited to the 647 nm laser line. For stable signal generation in imaging and flow cytometry, Alexa Fluor 647 dye is pH-insensitive over a wide molar range. Probes with high fluorescence quantum yield and high photostability allow detection of low-abundance biological structures with great sensitivity. Alexa Fluor 647 dye molecules can be attached to proteins at high molar ratios without significant self-quenching, enabling brighter conjugates and more sensitive detection. The degree of labeling for each conjugate is typically 2-8 fluorophore molecules per IgG molecule; the exact degree of labeling is indicated on the certificate of analysis for each product lot.


Using conjugate solutions: Centrifuge the protein conjugate solution briefly in a microcentrifuge before use; add only the

supernatant to the experiment. This step will help eliminate any protein aggregates that may have formed during storage, thereby reducing nonspecific background staining. Because staining protocols vary with application, the appropriate dilution of antibody should be determined empirically. For the fluorophore-labeled antibodies a final concentration of 1-10 µg/mL should be satisfactory for most immunohistochemistry and flow cytometry applications.

Product will be shipped at Room Temperature.


Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A-31571) in ICC /IF

mthfd1-1 mostly interferes with non-CG and H3K9 methylation. (a–c) Overlap between hypo-DMRs of different mutants in CG (a), CHG (b) and CHH (c) contexts. (d–f) CG (d), CHG (e) and CHH (f) methylation levels in DMR fractions corresponding to (a–c), respectively. w=wild-type, m=met1, t=*mthfd1-1*, c3=cmt3, c2=cmt2, d=drm1,2. Box plot (herein and after): horizontal line, median; edges of boxes, 25th (bottom) and 75th (top) percentiles; error bars, minimum and maximum points within 1.5 × interquartile range. (g) Heat map of DNA methylation levels in *mthfd1-1* hypo-DMRs (rows) clustered by methylation levels. (h) Overlap of met1 or *mthfd1-1* CG hypo-DMRs with PCGs or TEs. (i) Fluorescence micrographs of representative nuclei from WT and *mthfd1-1*. DNA was stained with DAPI and H3K9me2 was immunostained using Alexa Fluor 647 as secondary antibody. Scale bar, 5 μm. (j) Number of nuclei classified by DAPI staining and H3K9me2 immunofluorescence. Image collected and cropped by CiteAb from the following publication (<http://www.nature.com/articles/ncomms11640>), licensed under a CC BY license.




Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A-31571) in ICC /IF

Immunofluorescence analysis of Donkey anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor® 647 conjugate was performed using HeLa cells stained with alpha Tubulin (236-10501) Mouse Monoclonal Antibody (Product # A11126). The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton™ X-100 for 10 minutes, blocked with 1% BSA for 1 hour and labeled with 2 μg/mL primary antibody for 3 hours at room temperature. Donkey anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor® 647 (Product # A-31571) was used at a concentration of 2 μg/mL in phosphate buffered saline containing 0.2% BSA for 45 minutes at room temperature, for detection of alpha Tubulin in the cytoplasm (Panel a: red). Nuclei (Panel b: blue) were stained with DAPI in SlowFade® Gold Antifade Mountant (Product # S36938). F-actin was stained with Alexa Fluor® 488 Phalloidin (Product # A12379), 1:300 (Panel c: green). Panel d represents the composite image. No nonspecific staining was observed with the secondary antibody alone (panel f), or with an isotype control (panel e). The images were captured at 60X magnification.



Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A-31571) in Flow

Flow cytometry analysis of Pax6 on human neural stem cells derived from PD-3 iPSCs using Gibco® PSC Neural Induction Medium (Product # A1647801). Cells were fixed, permeabilized, and then stained with a Pax6 polyclonal antibody (Product # 42-6600) at a 1:100 dilution and a Nestin mouse monoclonal antibody (Product # MA1-110) at a 1:100 dilution. After incubation of the primary antibodies for 1 hour on ice, the cells were stained with Alexafluor® 488-conjugated goat anti-rabbit IgG secondary antibody (Product # A-11034) and Alexafluor® 647-conjugated donkey anti-mouse IgG secondary antibody (Product # A-31571) at a dilution of 1:500 for 1 hour on ice. Flow cytometry analysis was performed using the Attune® Acoustic Focusing Cytometer (Product # 4469120). A representative 10,000 cells were acquired for each sample.



Blueberry juice augments exercise-induced neuroprotection in a Parkinson's disease model through modulation of GDNF levels. *IBRO Neurosci Rep* (2022)

Proteomic Alterations and Novel Markers of Neurotoxic Reactive Astrocytes in Human Induced Pluripotent Stem Cell Models. *Front Mol Neurosci* (2022)

A Plasmodium falciparum ATP-binding cassette transporter is essential for liver stage entry into schizogony. *iScience* (2022)

Centrin 2: A Novel Marker of Mature and Neoplastic Human Astrocytes. *Front Cell Neurosci* (2022)

Neutrophil extracellular traps regulate ischemic stroke brain injury. *J Clin Invest* (2022)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.