

Goat anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor Plus 800

Product Details	
Size	1 mg
Species Reactivity	Mouse
Host/Isotope	Goat / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	Alexa Fluor® Plus 800
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Liquid
Concentration	2 mg/mL
Purification	Affinity chromatography
Storage buffer	proprietary buffer, pH 6.5
Contains	0.016% Methylisothiazolone, 0.016% Bromonitrodioxane
Storage Conditions	4° C, store in dark
RRID	AB_2633279


Applications	Tested Dilution	Publications
Western Blot (WB)	0.02-0.1 µg/mL	1 Publication
Miscellaneous PubMed (Misc)	-	5 Publications

Product Specific Information

To minimize cross-reactivity, the goat anti-mouse IgG whole antibodies have been pre cross-adsorbed against bovine IgG, goat IgG, rabbit IgG, rat IgG, human IgG, and human serum. Cross-adsorption or pre-adsorption is a purification step to increase specificity of the antibody resulting in less background staining and cross-reactivity. The secondary antibody solution is passed through a column matrix containing immobilized serum proteins from potentially cross-reactive species. Only the nonspecific-binding secondary antibodies are captured in the column, and the highly specific secondaries flow through. Further passages through additional columns result in highly cross-adsorbed preparations of secondary antibody. The benefits of these extra steps are apparent in multiplexing/multicolor-staining experiments where there is potential cross-reactivity with other primary antibodies or in tissue/cell fluorescent staining experiments where there may be the presence of endogenous immunoglobulins.

Using conjugate solutions: Centrifuge the protein conjugate solution briefly in a microcentrifuge before use; add only the supernatant to the experiment. This step will help eliminate any protein aggregates that may have formed during storage, thereby reducing nonspecific background staining. Because staining protocols vary with application, the appropriate dilution of antibody should be determined empirically.

Product Images For Goat anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor Plus 800



Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A32730) in WB
Western blot analysis of protein disulphide-isomerase (PDI) and progesterone receptor complex (p23) was performed by loading 3-fold serial dilutions of A431 whole cell lysate (starting at 15 μ g) and 2 μ L of the PageRuler Prestained NIR Protein Ladder (Product # 26635) per well onto a 4-20% Tris-HCl polyacrylamide gel. Proteins were transferred to Nitrocellulose Membranes (Product # 88018) and blocked with Fluorescence Blocker for 30 min. Membranes were probed with a PDI monoclonal antibody (Product # MA3-019) at a dilution of 1:5000 and a p23 monoclonal antibody at a dilution of 1:1000 (Product # MA3-414) overnight at 4°C on a rocking platform, washed with TBST, and probed with an Invitrogen Alexa Fluor Plus 800 Goat anti-Mouse IgG secondary antibody (Product # A32730) at dilutions of 1:40,000 for 45 minutes. Blots were imaged on an Infrared fluorescence imaging system.

6 References

Western Blot (1)

Frontiers in molecular neuroscience

GLYX-13 Ameliorates Schizophrenia-Like Phenotype Induced by MK-801 in Mice: Role of Hippocampal NR2B and DISC1.

Authors: Zhou D,Lv D,Wang Z,Zhang Y,Chen Z,Wang C

Species
Not Applicable

Dilution
1:10000

Year
2019

Miscellaneous PubMed (5)

Molecular medicine reports

Paeonol inhibits the development of 1chloro2,4dinitrobenzeneinduced atopic dermatitis via mast and T cells in BALB/c mice.

"A32730 was used in Western Blotting to investigate the therapeutic potential of paeonol on atopic dermatitis."

Authors: Meng Y,Liu Z,Zhai C,Di T,Zhang L,Zhang L,Xie X,Lin Y,Wang N,Zhao J,Wang Y,Li P

Species
Not Applicable

Dilution
1:10,000

Year
2019

Molecular medicine reports

PADI4mediated epithelialmesenchymal transition in lung cancer cells.

"A32730 was used in Western Blotting to evaluate the expression of protein-arginine deiminase type-4 and its associated molecular signalling in lung cancer metastasis."

Authors: Liu M,Qu Y,Teng X,Xing Y,Li D,Li C,Cai L

Species
Not Applicable

Dilution
1:2,000

Year
2019

[View more Misc references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.