

# Goat anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor™ Plus 680

Product Details	
Size	1 mg
Species Reactivity	Rabbit
Host/Isotype	Goat / IgG
Class	Polyclonal
Type	Secondary Antibody
Conjugate	Alexa Fluor™ Plus 680
Excitation/Emission Max	687/704 nm
Immunogen	Gamma Immunoglobins Heavy and Light chains
Form	Liquid
Concentration	2 mg/mL
Purification	Affinity chromatography
Storage buffer	proprietary buffer, pH 6.5
Contains	0.016% Bromonitrodioxane, 0.016% Methylisothiazolone
Storage conditions	4° C, store in dark
RRID	AB_2633283



Applications	Tested Dilution	Publications
Western Blot (WB)	0.02-0.1 µg/mL	0 Publication
Immunocytochemistry (ICC/IF)	1:2000	-
Flow Cytometry (Flow)	1:50	-
Miscellaneous PubMed (Misc)	-	0 Publication

## Product Specific Information

To minimize cross-reactivity, the goat anti-rabbit IgG whole antibodies have been pre cross-adsorbed against bovine IgG, goat IgG, mouse IgG, rat IgG, and human IgG. Cross-adsorption or pre-adsorption is a purification step to increase specificity of the antibody resulting in less background staining and cross-reactivity. The secondary antibody solution is passed through a column matrix containing immobilized serum proteins from potentially cross-reactive species. Only the nonspecific-binding secondary antibodies are captured in the column, and the highly specific secondaries flow through. Further passages through additional columns result in highly cross-adsorbed preparations of secondary antibody. The benefits of these extra steps are apparent in multiplexing/multicolor-staining experiments where there is potential cross-reactivity with other primary antibodies or in tissue/cell fluorescent staining experiments where there may be the presence of endogenous immunoglobulins.

Using conjugate solutions: Centrifuge the protein conjugate solution briefly in a microcentrifuge before use; add only the supernatant to the experiment. This step will help eliminate any protein aggregates that may have formed during storage, thereby reducing nonspecific background staining. Because staining protocols vary with application, the appropriate dilution of antibody should be determined empirically.

Product Images For Goat anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor™ Plus 680



Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A32734) in WB


Western blot analysis of Heat Shock Protein 90 (Hsp90) and histone deacetylase 1 (HDAC1) was performed by loading 3-fold serial dilutions of A431 whole cell lysate (starting at 15  $\mu$ g) and 2  $\mu$ L of the PageRuler Prestained NIR Protein Ladder (Product # 26635) per well onto a 4-20% Tris-HCl polyacrylamide gel. Proteins were transferred to Nitrocellulose Membranes (Product # 88018) and blocked with Fluorescence Blocker for 30 min. Membranes were probed with a Hsp90 polyclonal antibody (Product # PA3-013) at a dilution of 1:5000 and an HDAC1 polyclonal antibody at a dilution of 1:5000 (Product # PA1-1110) overnight at 4°C on a rocking platform, washed with TBST, and probed with an Invitrogen Alexa Fluor Plus 680 Goat anti-Rabbit IgG secondary antibody (Product # A32734) at dilutions of 1:40,000 for 45 minutes. Blots were imaged on an Infrared fluorescence imaging system.

Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A32734)

Specificity of secondary antibody was demonstrated by specific detection of the target immunoglobulin. Antibody specificity was demonstrated by specific detection of Rabbit IgG (H+L). A band at ~50 kDa and 25 kDa Heavy and Light Chain was observed in Rabbit IgG but not in other species using Goat anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor™ Plus 680 (Product # A32734) in Western Blot. Relative expression. {RE}

Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody (A32734) in WB

IFN1 secreted by CTX-treated cancer cells drives fibroblasts into an antiviral state and promotes recovery. (A) GSEA for HALLMARK showed interferon response as number one enriched term (left panel) in fibroblasts in CC with paclitaxel-treated cancer cells (CC-P) compared with untreated cancer cells (CC-U). Enrichment analysis using an independent gene set for IFNS in cancer [45] was also done (right panel). P values were determined by random permutation tests. (B) Heat-map with expression of significantly upregulated interferon transcripts in MCF7. Results for epirubicin (E)- and paclitaxel (P)-treated cancer cells are shown in log2 fold change and are normalized to untreated MCF7. (C) Layout of experimental setup for interferon KD experiments. (D, E) DDX58, IFIH1, ISG15 and OAS1 expression in CAF1 determined by RT-qPCR. CM from paclitaxel-treated MCF7 (n = 3, except for OAS1 where n = 2) (D) and HS578T (n = 2, except for ISG15 and OAS1 where n = 3) (E) transfected with a control siRNA (siCTRL), a siRNA against IFNB1 (siIFNB1) or a siRNA against IFNL1 (siIFNL1) was collected and added to CAF1. Relative fold change is normalized to CAF1 grown in DMEM. mRNA levels were normalized against two house-keeping genes (ACTB and PUM1). Each dot represents an independent experiment. P values for n > 2 were calculated using one-way ANOVA in biological replicates. \*P < 0.05, \*\*P < 0.01, \*\*\*P < 0.001. (F) Image collected and cropped by CiteAb from the following publication (<https://pubmed.ncbi.nlm.nih.gov/33476079>), licensed under a CC BY license.



View more figures on [thermofisher.com](https://thermofisher.com)

## 47 References

- Cdc42 couples septin recruitment to the axial landmark assembly via Axl2 in budding yeast. J Cell Sci (2024)
- A High-Protein Diet Promotes Atrial Arrhythmogenesis via Absent-in-Melanoma 2 Inflammasome. Cells (2024)
- Comprehensive chromatome profiling identifies metabolic enzymes on chromatin in healthy and cancer cells bioRxiv (2023)
- RUNX1 facilitates heart failure progression through regulating TGF--induced cardiac remodeling. PeerJ (2023)
- Investigation of the acetic acid stress response in *Saccharomyces cerevisiae* with mutated H3 residues. Microb Cell (2023)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.