

Plasminogen Monoclonal Antibody (8F11)

Catalog NumberMA1-20082

Product data sheet

Details		Species Reactivity	
Size	500 µg	Species reactivity	Human
Host/Isotope	Mouse / IgG1	Tested Applications	
Class	Monoclonal	Affinity Purification (AP)	Assay-dependent
Type	Antibody	ELISA (ELISA)	Assay-dependent
Clone	8F11	Immunohistochemistry (Paraffin) (IHC (P))	Assay-dependent
Immunogen	Purified, full length, native, human plasminogen protein.	* Suggested working dilutions are given as a guide only. It is recommended that the user titrate the product for use in their own experiment using appropriate negative and positive controls.	
Conjugate	Unconjugated		
Form	Liquid		
Concentration	8.3 mg/mL		
Storage Conditions	4° C		

Product specific information

MA1-20082 detects plasminogen in human samples.

Background/Target Information

Plasminogen is a plasma protein synthesized mostly in the liver. It consists of a single polypeptide chain and has a molecular weight of 88.5 kDa. The plasma concentration is usually in the range of 70 - 200 mg/L. Plasminogen is activated by tissue-plasminogen activator, urokinase and streptokinase, to form plasmin. Activation results from the cleavage and release of the preactivation peptide. Plasmin consists of a heavy (A-) chain which contains 5 kringles and a light (B-) chain with the active site. Plasmin is a trypsin-like protease whose natural substrate is fibrin, with binding sites for fibrin residing on the kringles. Plasmin is essential for fibrinolysis and decreased fibrinolytic potential due to congenital defects in plasmin can lead to recurring thrombosis, thrombophlebitis and pulmonary embolism.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization.

Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample.

NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.